

Product data sheet

Characteristics

PRM046252

Decor - buzzer - mechanism - 70 dB - 127 VAC - ivory sahara - 1 module



Main

Aesthetic name	Decor
Product or component type	Buzzer
Device presentation	Mechanism
Colour tint	Ivory sahara
Type of packing	Flow-pack

Complementary

[In] rated current	130 mA
Rated power in VA	16.5 VA
Acoustic level	70 dB
[Ue] rated operational voltage	127 V AC
Material	ABS (acrylonitrile butadiene-styrene)
Number of modules	1 module
Embedding depth	27.1 mm
Depth	36.1 mm
Length	43.4 mm
Height	36.1 mm
Width	23.5 mm
Connections - terminals	Pillar terminals
Cable cross section	X 6 mm ²
AWG gauge	AWG 8
Fixing mode	Clip-in

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1142 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
