

Product data sheet

Specifications



Decor - buzzer - mechanism - 70 dB
- 220 VAC - ivory sahara - 1 module

PRM046262

⚠ Discontinued on: Mar 31, 2023

⚠ Discontinued

Main

Aesthetic Name	Decor
Product Or Component Type	Buzzer
Device Presentation	Mechanism
Type Of Packing	Flow-pack

Complementary

[In] Rated Current	75 mA
Rated Power In Va	16.5 VA
Acoustic Level	70 dB
[Ue] Rated Operational Voltage	220 V AC
Material	ABS (acrylonitrile butadiene-styrene)
Number Of Modules	1 module
Embedding Depth	27.1 mm
Depth	36.1 mm
Length	43.4 mm
Height	36.1 mm
Width	23.5 mm
Connections - Terminals	Pillar terminals
Cable Cross Section	6 mm ²
Awg Gauge	AWG 8
Fixing Mode	Clip-in

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	9.5 cm
Package 1 Length	15.2 cm
Package 1 Weight	0.039 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations