



### Main

Aesthetic name	Decor
Product or component type	Control switch
Device presentation	Complete product
Colour tint	Ivory sahara
Type of packing	Flow-pack

### Complementary

Switch function	1-way
Local signalling	Without pilot light
[In] rated current	10 A
[Ue] rated operational voltage	250 V, AC
Material	ABS (acrylonitrile butadiene-styrene)
Number of modules	3
Embedding depth	24.9 mm
Depth	33.9 mm
Length	123 mm
Height	9 mm
Width	85 mm
Connections - terminals	Pillar terminals
Cable cross section	6 mm <sup>2</sup>
AWG gauge	AWG 8
Fixing mode	Clip-in

### Environment

Standards	ABNT NBR NM 60.669
-----------	--------------------

### Contractual warranty

Warranty period	18 months
-----------------	-----------