



Main

Aesthetic name	Decor
Product or component type	Control switch
Device presentation	Complete product
Colour tint	Graphite
Type of packing	Flow-pack

Complementary

Switch function	1-way
Local signalling	Without pilot light
[In] rated current	10 A
[Ue] rated operational voltage	250 V, AC
Material	ABS (acrylonitrile butadiene-styrene)
Number of modules	3
Embedding depth	24.9 mm
Depth	33.9 mm
Length	123 mm
Height	9 mm
Width	85 mm
Connections - terminals	Pillar terminals
Cable cross section	6 mm ²
AWG gauge	AWG 8
Fixing mode	Clip-in

Environment

Standards	ABNT NBR NM 60.669
-----------	--------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1142 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------