



Main

| | |
|---------------------------|------------------|
| Aesthetic name | Decor |
| Product or component type | Control switch |
| Device presentation | Complete product |
| Colour tint | Ivory sahara |
| Type of packing | Flow-pack |

Complementary

| | |
|--------------------------------|---------------------------------------|
| Switch function | Double 2-way |
| Local signalling | Without pilot light |
| [In] rated current | 10 A |
| [Ue] rated operational voltage | 250 V, AC |
| Material | ABS (acrylonitrile butadiene-styrene) |
| Number of modules | 3 |
| Embedding depth | 24.9 mm |
| Depth | 33.9 mm |
| Length | 123 mm |
| Height | 9 mm |
| Width | 85 mm |
| Connections - terminals | Pillar terminals |
| Cable cross section | 6 mm ² |
| AWG gauge | AWG 8 |
| Fixing mode | Clip-in |

Environment

| | |
|-----------|--------------------|
| Standards | ABNT NBR NM 60.669 |
|-----------|--------------------|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|