



### Main

|                           |                  |
|---------------------------|------------------|
| Aesthetic name            | Decor            |
| Product or component type | Buzzer           |
| Device presentation       | Complete product |
| Colour tint               | Ivory sahara     |
| Type of packing           | Flow-pack        |

### Complementary

|                                |                                       |
|--------------------------------|---------------------------------------|
| [In] rated current             | 130 mA                                |
| Rated power in VA              | 16 VA                                 |
| Acoustic level                 | 70 dB                                 |
| [Ue] rated operational voltage | 127 V AC                              |
| Material                       | ABS (acrylonitrile butadiene-styrene) |
| Number of modules              | 3 modules                             |
| Embedding depth                | 27.1 mm                               |
| Depth                          | 36.1 mm                               |
| Length                         | 123 mm                                |
| Height                         | 9 mm                                  |
| Width                          | 85 mm                                 |
| Connections - terminals        | Pillar terminals                      |
| Cable cross section            | X 6 mm <sup>2</sup>                   |
| AWG gauge                      | AWG 8                                 |
| Fixing mode                    | Clip-in                               |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|