

# Product data sheet

## Characteristics

# PRMS044083

Decor - buzzer - complete product - 70 dB - 127  
VAC - graphite



### Main

Range	Prime
Aesthetic name	Decor
Product or component type	Buzzer
Device application	Signalling
Device presentation	Complete product
Colour tint	Graphite
Type of packing	Flow-pack

### Complementary

[In] rated current	130 mA
Rated power in VA	16 VA
Acoustic level	70 dB
[Ue] rated operational voltage	120 V AC
Material	ABS (acrylonitrile butadiene-styrene)
Number of modules	3 modules
Embedding depth	27.1 mm
Depth	36.1 mm
Length	123 mm
Height	9 mm
Width	85 mm
Connections - terminals	Pillar terminals
Cable cross section	X 6 mm <sup>2</sup>
AWG gauge	AWG 8
Fixing mode	Clip-in

### Environment

Environmental characteristic	UV protection
------------------------------	---------------

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity
------------------------	---

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---