



Main

Range	Resi9
Product or component type	Door
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 enclosure

Complementary

Type of front cover	Opaque
Number of horizontal rows	1
Number of 18 mm modules per row	13
Total number of 18 mm modules	13
Standards	IEC 61439-3 IEC 60670-1-24 IEC 61439-1
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to EN 50102 IK08 conforming to IEC 62262
Product weight	400 g
Width	247.5 mm
Height	245.5 mm
Depth	27 mm
Colour tint	White (RAL 9003)

Environment

Ambient air temperature for operation	-15...60 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1623 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information