



### Main

Range	Resi9
Product or component type	Partition wall
Range compatibility	Opale Resi9
Standards	NFC 15-100 NF EN 50085-2-1

### Complementary

Quantity per set	Set of 10
------------------	-----------

### Environment

IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to EN 50102 IK08 conforming to IEC 62262
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
Height	2600 mm
Colour	White (RAL 9003)

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1623 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications