



### Main

Range	Resi9
Product or component type	Door
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 enclosure

### Complementary

Type of front cover	Transparent
Number of horizontal rows	3
Number of 18 mm modules per row	18
Total number of 18 mm modules	54
Standards	IEC 61439-3 IEC 61439-1 IEC 60670-1-24
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to EN 50102 IK08 conforming to IEC 62262
Product weight	850 g
Width	352.5 mm
Height	495.5 mm
Depth	27 mm
Colour tint	Transparent

### Environment

Ambient air temperature for operation	-15...60 °C
---------------------------------------	-------------

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1623 - Schneider Electric declaration of conformity

---

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

---