

Product data sheet

Specifications



P115 self power - In 5A - Ion 1A 0.05-10Ion - no Vx

REL10123

⚠ Discontinued on: Dec 31, 2023

⚠ To be end-of-service on: Dec 31, 2031

⚠ Discontinued

Main

Range Of Product	MiCOM P11x
Device Short Name	P115
Relay Application	Feeder
Input Output Max Capacity	2 inputs + 4 outputs
Communication Port Protocol	IEC 60870-5-103 Modbus RTU

Complementary

Type Of Measurement	Current
Auxiliary Supply	60...240 V AC 60...250 V DC
Display Type	LCD display: 2 lines of 16 characters ASCII (European characters) and 9 key
Earth Current Inputs	5 A 0.2...40 In 5 A
Communication Port Support	USB RS485

Environment

Device Mounting	Flush
Mounting Mode	Flush-mounted

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.8 cm
Package 1 Width	15.8 cm
Package 1 Length	25.6 cm
Package 1 Weight	2.14 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications