



Main

Range	Miluz
Aesthetic name	White moulded
Product or component type	Switch
Device presentation	Mechanism
Colour tint	Polar white (RAL 9003)
Type of packing	Flow-pack

Complementary

Switch function	2-pole 1-way
Local signalling	Without pilot light
Marking	1 - 2 - L1 - L2
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Material	ABS (acrylonitrile butadiene-styrene); wiring device
Number of modules	1 module
Fixing mode	Clip-in
Connections - terminals	Screw-clamp terminals
Cable cross section	4 mm ²
AWG gauge	AWG 12
Height	20 mm
Width	41.4 mm
Depth	36 mm
Embedding depth	26 mm
Projecting depth	10 mm

Environment

Standards	ABNT NBR NM 60.669
-----------	--------------------

Product certifications	NOM/ANCE RETIE
------------------------	-------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations