



### Main

Range of product	Odace
Product or component type	SAT single shield
Device presentation	Mechanism with plastic fixing frame
Type of packing	Paint cover
Quantity per set	Set of 5

### Complementary

Device mounting	Flush
SAT connector	F type
Path attenuation	1.5 dB for SAT signal @ 950...2150 MHz
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Connections - terminals	Screw
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	PBT (polybutylene terephthalate) GF30 support frame Thermoplastic ABS-UV stabilised centre plate Zinc alloy casing
Height	71 mm
Width	71 mm
Depth	34.1 mm
Embedding depth	18.1 mm
Product weight	0.042 kg

### Environment

Ambient air temperature for storage	-5...50 °C
-------------------------------------	------------

Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4 2006/95/EC
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1148 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------