

Product data sheet

Specifications

Odace - LED - white - 8 mA, 250 V AC - wire



S520739

Main

| | |
|------------------------------|------------------|
| Range Of Product | Odace |
| Product Or Component Type | LED |
| Product Specific Application | Replacement lamp |
| Type Of Packing | Plastic bag |

Complementary

| | |
|--------------------------------|--|
| Light Source Colour | White |
| Product Destination | For Styl outer plate label holder |
| Fixing Mode | Clip-in |
| Colour Tint | White (RAL 9003) |
| Temperature Rise | 25 °C |
| Service Life In Hours | 64000 h (L70) 55 lux |
| [Ue] Rated Operational Voltage | 250 V AC 50/60 Hz |
| Current Consumption | 8 mA |
| Number Of Cables | 2 |
| Material | ABS (acrylonitrile butadiene-styrene): support cover PC (polycarbonate): screen |
| Embedding Depth | 8.7 mm |
| Net Weight | 0.011 kg |

Environment

| | |
|---------------------------------------|-------------|
| Ambient Air Temperature For Storage | -5...50 °C |
| Ambient Air Temperature For Operation | 5...45 °C |
| Standards | 2006/95/EEC |
| Product Certifications | N |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.0 cm |
| Package 1 Width | 3.0 cm |
| Package 1 Length | 9.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Package 1 Weight | 13.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 4.8 cm |
| Package 2 Width | 10.7 cm |
| Package 2 Length | 16.3 cm |
| Package 2 Weight | 64.0 g |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 56 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 2.233 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Lower Impact Materials Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Minimum Percentage Of Recycled Plastic Content 28

✓ Sustainable Packaging

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |