



Main

Range of product	Odace
Product or component type	Telephone socket
Device presentation	Mechanism with plastic fixing frame
Telephone socket type	France Telecom 8 contact(s)
Quantity per set	Set of 1
Condition of use	Indoor

Complementary

Wiring device mounting	Flush
Device mounting	Flush
Fixing mode	Screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Connections - terminals	Screw terminals
Number of loop terminals	1
Material	PBT (polybutylene terephthalate) GF30 support frame Thermoplastic ABS-UV stabilised centre plate
Height	71 mm
Width	71 mm
Depth	27.7 mm
Embedding depth	11.7 mm
Product weight	0.037 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	CENET 28417 Ed3

	EN 60529
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Ammonia UV resistant Window-cleaning fluid Bleach Oil Petrol Acetone Liquid soap Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------