



Main

| | |
|-------------------------------|---------------------|
| Range of product | Odace |
| Aesthetic name | Touch |
| Product or component type | Cover frame |
| Number of gangs | 2 gangs |
| Installation direction | Horizontal/vertical |
| Distance between centers | 71 mm |
| Type of frame | Double |
| Type of packing | Flow-pack |
| Quantity per set | Set of 5 |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|-----------------|----------------------------|
| Device mounting | Flush |
| Fixing mode | Clip-in |
| Colour tint | Black astrakhan oak |
| Material | PC (polycarbonate) Wood |
| Height | 85 mm |
| Width | 156 mm |
| Depth | 10 mm |
| Net weight | 0.02176 kg |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -5...50 °C |
| Ambient air temperature for operation | 5...45 °C |
| Standards | NF C 61-314 2006/95/EEC EN 60669-1 |

UNE 20315-1-1
NBN C 61-112-1

| | |
|---------------------------------|---|
| Product certifications | N NF |
| IK degree of protection | IK04 |
| IP degree of protection | IP21D |
| Environmental characteristic | Petrol UV resistant Liquid soap Ammonia Bleach Alcohol Window-cleaning fluid Acetone |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|