

# Product data sheet

Specifications



## Cover frame, Odace Touch, 3 gangs, black

S530806P1

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Number Of Gangs	3 gangs
Installation Direction	Horizontal/vertical
Distance Between Centers	71 mm
Type Of Frame	Triple
Type Of Packing	Flow-pack

### Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Black astrakhan oak
Side Color	Aluminium
Surface Finish	Matt
Material	PC (polycarbonate) Wood
Height	85 mm
Width	227 mm
Depth	10 mm
Net Weight	0.03062 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NF C 61-314 2006/95/EEC NBN C 61-112-1 UNE 20315-1-1 EN 60669-1
Product Certifications	N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	8.500 cm
Package 1 Length	23.000 cm
Package 1 Weight	50.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	5.800 cm
Package 2 Width	9.000 cm
Package 2 Length	37.000 cm
Package 2 Weight	316.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.420 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations