



### Main

Range of product	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Number of gangs	2 gangs
Installation direction	Vertical
Distance between centers	57 mm
Type of frame	Double
Type of packing	Flow-pack
Quantity per set	Set of 5
Sale per indivisible quantity	1

### Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	Black astrakhan oak
Material	PC (polycarbonate) Wood
Height	142 mm
Width	85 mm
Depth	10 mm
Net weight	0.01924 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	UNE 20315-1-1 NBN C 61-112-1 NF C 61-314

EN 60669-1  
2006/95/EEC

Product certifications	N NF
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Oil UV resistant Ammonia Alcohol Petrol Acetone Liquid soap Window-cleaning fluid Bleach
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------