



Main

Range of product	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Number of gangs	2 gangs
Installation direction	Horizontal/vertical
Distance between centers	71 mm
Type of frame	Double
Type of packing	Flow-pack
Quantity per set	Set of 5
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	Anthracite and glossy fume
Surface finish	Glossy
Material	Aluminium: decorative frame PC (polycarbonate)
Height	85 mm
Width	156 mm
Depth	10 mm
Net weight	0.02176 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	NBN C 61-112-1 2006/95/EEC

UNE 20315-1-1
EN 60669-1
NF C 61-314

Product certifications	N NF
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Alcohol Liquid soap UV resistant Petrol Window-cleaning fluid Acetone Ammonia Bleach
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------