

Product data sheet

Specifications



Cover frame, Odace Touch, 2 gangs, anthracite

S540804P3

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Number Of Gangs	2 gangs
Installation Direction	Horizontal/vertical
Distance Between Centers	71 mm
Type Of Frame	Double
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Wood ash
Side Color	Anthracite
Surface Finish	Matt
Material	PC (polycarbonate): decorative frame Aluminium
Height	85 mm
Width	156 mm
Depth	10 mm
Net Weight	0.02176 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NBN C 61-112-1 2006/95/EEC EN 60669-1 NF C 61-314 UNE 20315-1-1
Product Certifications	AENOR: 030/2205 LCIE: NF 603415A N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.5 cm
Package 1 Length	15.6 cm
Package 1 Weight	32 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9 cm
Package 2 Width	5.8 cm
Package 2 Length	37 cm
Package 2 Weight	229 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	30
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	1.714 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations