

Product data sheet

Specifications



Orion - duplex American socket outlet 2P+E 15A 120/125/127V~ GFCI with fixing frame white

S703270045

Main

Range Of Product	Orion
Range	Orion
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with fixing frame
Outlet Poles Configuration	2P + E with shutter
Fixing Mode	By screws
Type Of Packing	Flow-pack
Sale Per Indivisible Quantity	1
Rated Current	15 A at 125 V AC 60 Hz

Complementary

Device Mounting	Flush
Outlet Standard	American
Outlet Standard Description	GFCI
Ground Lug Position	Straight 0° position
Number Of Modules	3 modules 120 x 82.5 mm
Local Signalling	LED (red/orange) for trip/end of life
Surface Finish	Glossy
Surface Treatment	Untreated
Ambient Air Temperature For Storage	-20...60 °C
Protection Type	Earth-leakage protection
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Electrical Durability	5000 cycles
Connections - Terminals	3 screw-clamp terminals
Clamping Connection Capacity	1.5...4 mm² for rigid cable(s) 1.5...4 mm² for stranded cable(s) 1.5...4 mm² for flexible cable(s)
Wire Stripping Length	18 mm
Material	PC (polycarbonate) FR: casing PC (polycarbonate) FR: centre plate ABS (acrylonitrile butadiene-styrene): adaptor frame
Height	113 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	71 mm
Depth	40 mm
Embedding Depth	30.6 mm
Standards	UL 94 UL 943 UL 498 NMX J-508 ANCE

Environment

Product Certifications	NOM
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Environmental Characteristic	Hydrogen peroxide (H2O2) Oil Alcohol Acetone Petrol Bleach Window-cleaning fluid UV resistant Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	7.5 cm
Package 1 Length	20.0 cm
Package 1 Weight	136.0 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)