



Main

Range of product	Orion
Range	Orion
Product or component type	Switch
Device presentation	Complete product
Provided equipment	Fixing frame Cover frame
Device application	Lighting
Colour tint	Beige Pantone 7530C
Type of packing	Flow-pack
Quantity per set	Set of 20
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Switch function	1-pole 2-way
Number of modules	1 module
Number of rocker	1
Actuator	Rocker
Surface finish	Glossy
Surface treatment	Untreated
Rated current	16 AX 127/250 V AC 50/60 Hz
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un
Electrical durability	20000 cycles IEC 60669
Connections - terminals	Screw terminals 3
Shape of screw head	Pozidriv No 2
Clamping connection capacity	1.5...4 mm ² rigid 1.5...4 mm ² stranded 1.5...4 mm ² flexible
Wire stripping length	11 mm
Local signalling	LED optional
Material	Stainless steel spring Steel screw Thermoplastic ABS-UV stabilised mechanism rocker

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

PC (polycarbonate) GF10 FR cover
 PA (polyamide) 66 GF25 FR inner rocker
 Silver alloy contact
 Brass terminals
 Steel nut
 PC (polycarbonate) GF10 FR casing

Height	82.5 mm
Width	120 mm
Depth	37 mm
Embedding depth	25.1 mm

Environment

Ambient air temperature for storage	-5...40 °C
Dielectric strength	2000 V
Ambient air temperature for operation	-5...35 °C
Product certifications	INMETRO NOM/ANCE INGCER
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1450 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations