

# Product data sheet

Specifications



Orion - assembled 3 italian socket outlet 2P+E 10A 250V ivory / horizon gold

S713328234

## Main

Range Of Product	Orion
Range	Orion
Product Or Component Type	Socket-outlet
Device Presentation	Complete product
Outlet Poles Configuration	2P + E with shutter
Fixing Mode	By screws
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Sale Per Indivisible Quantity	1
Rated Current	10 A at 250 V AC 50/60 Hz

## Complementary

Number Of Power Socket Outlets	3
Device Mounting	Flush
Outlet Standard Description	With earthing contact
Outlet Standard	Italian
Ground Lug Position	Straight 0° position
Number Of Modules	3 modules 120 x 82.5 mm
Surface Finish	Glossy
Surface Treatment	Untreated
Ambient Air Temperature For Storage	-5...50 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Electrical Durability	5000 cycles
Connections - Terminals	3 screw terminals
Screwdriver Shape	Pozidriv No 2
Number Of Cables	2
Clamping Connection Capacity	1...4 mm² for rigid cable(s) 1...4 mm² for stranded cable(s) 1...4 mm² for flexible cable(s)
Wire Stripping Length	11 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	ASA + PC: mechanism cover PC (polycarbonate) GF10 FR: casing PS (polystyrene): fixing frame Thermoplastic ABS-UV stabilised: cover frame
Height	120 mm
Width	82.5 mm
Depth	32.55 mm
Embedding Depth	23.95 mm
Net Weight	0.0958 kg
Standards	NCh 2027/2 NCh 2027/1

## Environment

Product Certifications	INGCER
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Alcohol Hydrogen peroxide (H2O2) UV resistant Liquid soap Window-cleaning fluid Oil Acetone Petrol Bleach

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	9.3 cm
Package 1 Length	20.0 cm
Package 1 Weight	98.0 g

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Reach Free Of Svhc

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)