

# Product data sheet

Specifications



## Orion - assembled duplex American socket outlet 2P+E isolated 20A 250V hospital

S713340N45

⚠ Discontinued on: Dec 15, 2022

⚠ Discontinued

### Main

|                               |                           |
|-------------------------------|---------------------------|
| Range Of Product              | Orion                     |
| Range                         | Orion                     |
| Product Or Component Type     | Socket-outlet             |
| Device Presentation           | Complete product          |
| Outlet Poles Configuration    | 2P + E without shutter    |
| Fixing Mode                   | By screws                 |
| Type Of Packing               | Flow-pack                 |
| Quantity Per Set              | Set of 10                 |
| Sale Per Indivisible Quantity | 1                         |
| Rated Current                 | 20 A at 125 V AC 50/60 Hz |

### Complementary

|                                       |                                                                                                          |
|---------------------------------------|----------------------------------------------------------------------------------------------------------|
| Number Of Power Socket Outlets        | 2                                                                                                        |
| Device Mounting                       | Flush                                                                                                    |
| Outlet Standard Description           | Isolated earth<br>Hospital grade                                                                         |
| Outlet Standard                       | American                                                                                                 |
| Ground Lug Position                   | Straight 0° position                                                                                     |
| Number Of Modules                     | 3 modules 120 x 82.5 mm                                                                                  |
| Surface Finish                        | Glossy                                                                                                   |
| Surface Treatment                     | Untreated                                                                                                |
| Ambient Air Temperature For Storage   | -20...60 °C                                                                                              |
| Dielectric Strength                   | 2000 V                                                                                                   |
| Ambient Air Temperature For Operation | -5...35 °C                                                                                               |
| Electrical Durability                 | 5000 cycles                                                                                              |
| Connections - Terminals               | 3 screw terminals                                                                                        |
| Screwdriver Shape                     | Philips                                                                                                  |
| Number Of Cables                      | 2                                                                                                        |
| Clamping Connection Capacity          | 1.5...4 mm² for rigid cable(s)<br>1.5...4 mm² for stranded cable(s)<br>1.5...4 mm² for flexible cable(s) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                       |                                                                                                                                                                |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire Stripping Length | 18 mm                                                                                                                                                          |
| Material              | PA (polyamide): casing<br>PA (polyamide): centre plate<br>ABS (acrylonitrile butadiene-styrene): adaptor frame<br>Thermoplastic ABS-UV stabilised: cover frame |
| Height                | 120 mm                                                                                                                                                         |
| Width                 | 82.5 mm                                                                                                                                                        |
| Depth                 | 38.2 mm                                                                                                                                                        |
| Embedding Depth       | 28.5 mm                                                                                                                                                        |
| Net Weight            | 0.138 kg                                                                                                                                                       |
| Standards             | UL 498<br>UL 94                                                                                                                                                |

## Environment

|                              |                                                                                                                                   |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Product Certifications       | NOM                                                                                                                               |
| Ik Degree Of Protection      | IK04                                                                                                                              |
| Ip Degree Of Protection      | IP20                                                                                                                              |
| Environmental Characteristic | Acetone<br>Oil<br>UV resistant<br>Window-cleaning fluid<br>Petrol<br>Alcohol<br>Liquid soap<br>Bleach<br>Hydrogen peroxide (H2O2) |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 4.0 cm  |
| Package 1 Width              | 9.3 cm  |
| Package 1 Length             | 20.0 cm |
| Package 1 Weight             | 136.0 g |