



Main

Range	Orion
Aesthetic name	Orion Essence
Product or component type	Cover frame

Complementary

Device mounting	Flush
Number of gangs	1 gang
Number of modules	1 module
Fixing mode	Clip-in
Colour tint	Planet brown (Pantone 8425C)
Surface finish	Matt
Surface treatment	Painted
Type of packing	Flow-pack
Quantity per set	Set of 20
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	82.5 mm
Depth	7.9 mm
Net weight	0.0202 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	UV resistant Window-cleaning fluid Oil Bleach Ammonia Liquid soap Petrol Alcohol

	Acetone Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations