

Product data sheet

Specifications



Orion - blind cover 4X4 - stellar black

S730200294

Main

Range	Orion
Aesthetic Name	Orion Essence
Product Or Component Type	Blind cover

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Stellar black (RAL 7021)
Surface Finish	Matt
Surface Treatment	Painted
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	127.5 mm
Depth	7.9 mm
Net Weight	0.0331 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D
Environmental Characteristic	Window-cleaning fluid Bleach Oil Liquid soap UV resistant Petrol Acetone Alcohol Hydrogen peroxide (H2O2)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.8 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	31.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
