

Product data sheet

Specifications



Orion - cover-frame 4X4 - 2 modules - antibacterian - white

S730201024

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Orion
Aesthetic Name	Orion Essence
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Number Of Gangs	2 gangs
Number Of Modules	2 x 1 module
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003)
Surface Finish	Glossy
Surface Treatment	Antibacterial
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	127.5 mm
Depth	7.9 mm
Net Weight	0.0293 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D
Environmental Characteristic	Oil Petrol Liquid soap Alcohol Bleach Hydrogen peroxide (H2O2) Window-cleaning fluid Acetone UV resistant

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	31.0 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Under investigation

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations