



Main

Range	Orion
Aesthetic name	Orion Essence
Product or component type	Cover frame

Complementary

Device mounting	Flush
Number of gangs	2 gangs
Number of modules	2 x 1 module
Fixing mode	Clip-in
Colour tint	Gamma silver (RAL 9006)
Surface finish	Matt
Surface treatment	Painted
Type of packing	Flow-pack
Quantity per set	Set of 20
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	120 mm
Width	127.5 mm
Depth	7.9 mm
Product weight	0.0293 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant

Window-cleaning fluid
Hydrogen peroxide (H2O2)

Environmental health and issues	Halogen free
---------------------------------	--------------

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1450 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Product environmental profile	Available Product Environmental Profile
-------------------------------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------
