



### Main

Range	Orion
Aesthetic name	Orion materials chrome
Product or component type	Cover frame

### Complementary

Device mounting	Flush
Number of gangs	1 gang
Number of modules	6 modules
Fixing mode	Clip-in
Colour tint	Chrome satin (Pantone 8402C) White (RAL 9003)
Surface finish	Glossy
Surface treatment	Painted
Type of packing	Blister
Quantity per set	Set of 10
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	127.5 mm
Width	120 mm
Depth	8.3 mm
Product weight	0.0294 kg

### Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol

UV resistant  
Window-cleaning fluid  
Hydrogen peroxide (H2O2)

---

Environmental health and issues

Halogen free

---