

# Product data sheet

Specifications



## Orion - cover-frame 4X4 - 6 modules - white / chrome satin

S732203419

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	Orion
Aesthetic Name	Orion materials chrome
Product Or Component Type	Cover frame

### Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Modules	6 modules
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003) Chrome satin (Pantone 8402C)
Surface Finish	Glossy
Surface Treatment	Painted
Type Of Packing	Blister
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	127.5 mm
Width	120 mm
Depth	8.3 mm
Net Weight	0.0294 kg

### Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D
Environmental Characteristic	Oil Alcohol Acetone Petrol Bleach UV resistant Window-cleaning fluid Liquid soap Hydrogen peroxide (H2O2)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	15 cm
Package 1 Length	17 cm
Package 1 Weight	72 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16 cm
Package 2 Width	15.2 cm
Package 2 Length	25.9 cm
Package 2 Weight	715 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---