



Main

Range	Orion
Aesthetic name	Orion materials aluminium
Product or component type	Blind cover

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	Aluminium magma copper (Pantone 8021C) White (RAL 9003)
Surface finish	Metallic
Surface treatment	Metallic
Type of packing	Flow-pack
Quantity per set	Set of 10
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame Metal
Height	120 mm
Width	82.5 mm
Depth	8.3 mm
Product weight	0.032 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid

Hydrogen peroxide (H₂O₂)

Environmental health and issues

Halogen free
