


Product data sheet

Specifications



Orion - cover-frame 4X2 - 3 modules - white / aluminium solar yellow

S733103609

 **Discontinued on:** Dec 15, 2022

 **Discontinued**

Main

Range	Orion
Aesthetic Name	Orion materials aluminium
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Modules	3 modules
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003) Aluminium solar yellow (Pantone 586C)
Surface Finish	Metallic
Surface Treatment	Metallic
Type Of Packing	Blister
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame Metal
Height	120 mm
Width	82.5 mm
Depth	8.3 mm
Net Weight	0.0233 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Oil
	Acetone
	Liquid soap
	Alcohol
	Hydrogen peroxide (H2O2)
	Bleach
	Petrol
	UV resistant
	Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	12.5 cm
Package 1 Length	17 cm
Package 1 Weight	52 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16 cm
Package 2 Width	15.2 cm
Package 2 Length	25.9 cm
Package 2 Weight	515 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
