



Main

Range	Orion
Aesthetic name	Orion materials aluminium
Product or component type	Cover frame

Complementary

Device mounting	Flush
Number of gangs	1 gang
Number of modules	3 modules
Fixing mode	Clip-in
Colour tint	Aluminium orbital blue (Pantone 629C) White (RAL 9003)
Surface finish	Metallic
Surface treatment	Metallic
Type of packing	Flow-pack
Quantity per set	Set of 10
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame Metal
Height	82.5 mm
Width	120 mm
Depth	8.3 mm
Product weight	0.0233 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil

Petrol
UV resistant
Window-cleaning fluid
Hydrogen peroxide (H2O2)

Environmental health and issues

Halogen free

Offer Sustainability

RoHS (date code: YYWW)

Compliant - since 1450 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

Product environmental profile

Available

 [Product Environmental Profile](#)

Product end of life instructions

Need no specific recycling operations
