



### Main

Range	Orion
Aesthetic name	Orion materials aluminium
Product or component type	Cover frame

### Complementary

Device mounting	Flush
Number of gangs	2 gangs
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Aluminium aurora gold (Pantone 8360C) White (RAL 9003)
Surface finish	Metallic
Surface treatment	Metallic
Type of packing	Flow-pack
Quantity per set	Set of 10
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame Metal
Height	82.5 mm
Width	120 mm
Depth	8.3 mm
Product weight	0.0259 kg

### Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil

Petrol  
UV resistant  
Window-cleaning fluid  
Hydrogen peroxide (H2O2)

Environmental health and issues

Halogen free

### Offer Sustainability

RoHS (date code: YYWW)

Compliant

 [Schneider Electric declaration of conformity](#)

Product environmental profile

Available

 [Product Environmental Profile](#)

Product end of life instructions

Need no specific recycling operations