

Product data sheet

Specifications



Orion - cover & fixing-frame 4X2 - 1 module - ivory

S735101014

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Orion
Aesthetic Name	Orion Essence
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Provided Equipment	Fixing frame
Number Of Gangs	1 gang
Number Of Modules	1 module
Fixing Mode	Clip-in
Colour Tint	Ivory (RAL 1013)
Surface Finish	Glossy
Surface Treatment	Untreated
Type Of Packing	Flow-pack
Quantity Per Set	Set of 30
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	82.5 mm
Depth	19.5 mm
Net Weight	0.0378 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Liquid soap
	Hydrogen peroxide (H2O2)
	Bleach
	UV resistant
	Alcohol
	Petrol
	Acetone
	Oil
	Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	9.3 cm
Package 1 Length	20.0 cm
Package 1 Weight	40.0 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Under investigation

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations