



Main

Range	Orion
Aesthetic name	Orion Essence
Product or component type	Cover frame

Complementary

Device mounting	Flush
Provided equipment	Fixing frame
Number of gangs	1 gang
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	White (RAL 9003)
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Flow-pack
Quantity per set	Set of 15
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	82.5 mm
Width	120 mm
Depth	19.5 mm
Product weight	0.0363 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol

UV resistant
Window-cleaning fluid
Hydrogen peroxide (H2O2)

Environmental health and issues

Halogen free

Offer Sustainability

RoHS (date code: YYWW)

Compliant - since 1450 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

Product environmental profile

Available

 [Product Environmental Profile](#)

Product end of life instructions

Need no specific recycling operations