



Main

Range	Orion
Aesthetic name	Orion Essence
Product or component type	Cover frame

Complementary

Device mounting	Flush
Provided equipment	Fixing frame
Number of gangs	1 gang
Number of modules	3 modules
Fixing mode	Clip-in
Colour tint	Black
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Flow-pack
Quantity per set	Set of 30
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	82.5 mm
Width	120 mm
Depth	19.5 mm
Product weight	0.0389 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol

UV resistant
Window-cleaning fluid
Hydrogen peroxide (H2O2)

Environmental health and issues

Halogen free
