


Product data sheet

Specifications



Orion - cover & fixing-frame 4X2 - 2 modules - black

S735121084

 **Discontinued on:** Dec 11, 2019

 **Discontinued**

Main

Range	Orion
Aesthetic Name	Orion Essence
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Provided Equipment	Fixing frame
Number Of Gangs	2 gangs
Number Of Modules	2 x 1 module
Fixing Mode	Clip-in
Colour Tint	Black
Surface Finish	Glossy
Surface Treatment	Untreated
Type Of Packing	Flow-pack
Quantity Per Set	Set of 30
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	82.5 mm
Depth	19.5 mm
Net Weight	0.0389 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Hydrogen peroxide (H2O2)
	Alcohol
	Window-cleaning fluid
	Acetone
	Oil
	Liquid soap
	Bleach
	UV resistant
	Petrol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	38 g