



Main

Range	Sequence5
Product or component type	Reading lamp
Device application	Reading
Device mounting	Flush
Device presentation	Complete product
Switch function	2-way

Complementary

Rated lamp wattage	3 W
Bulb type	LED
Rated current	10 A - 250 V AC 50 Hz
Number of terminals	4
Shape of screw head	Hexagonal
Material	Metal
Colour tint	Nickel
Surface finish	Glossy
Type of packing	Box
Quantity per set	1
Sale per indivisible quantity	1
Height	80 mm
Width	160 mm
Depth	311 mm
Embedding depth	35 mm
Product weight	0.651 kg

Environment

IP degree of protection	IP20
-------------------------	------