



### Main

Range of product	Sequence5
Product or component type	1 socket-outlet
Device presentation	Complete product
Type of packing	Box
Quantity per set	1
Sale per indivisible quantity	1
Number of terminals	3

### Complementary

Device mounting	Flush
Outlet poles configuration	2P + E with shutters
Outlet standard description	Pin earth
Outlet standard	French
Fixing mode	By screws
Colour tint	Copper
Surface finish	Glossy
Rated current	16 A - 250 V AC 50 Hz
Service life in cycles	5000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 4 mm <sup>2</sup> rigid cable(s) 1 x 1.5...2 x 4 mm <sup>2</sup> stranded cable(s) 1 x 1.5...2 x 4 mm <sup>2</sup> flexible cable(s)
Wire stripping length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	39.5 mm
Embedding depth	35 mm
Product weight	0.167 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	NF C 61-314
Product certifications	NF LCIE : NF 603415A
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free