



Main

Range of product	Sequence5
Device presentation	Complete product
Type of packing	Box
Quantity per set	Set of 1

Complementary

Device mounting	Flush
Colour tint	Brushed gold
Surface finish	Glossy
Rated current	6 A - 250 V AC 50/60 Hz
Protection type	Fuse 16 A
Number of terminals	1 screw 4 screwless terminals
Shape of screw head	Hexagonal
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	13 mm
Light source	LED
Height	115 mm
Width	80 mm
Depth	48 mm
Embedding depth	38 mm
Product weight	0.284 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Product certifications	NF CE
IP degree of protection	IP20