



Main

Range of product	Sequence5
Product or component type	Push-button
Device presentation	Complete product
Switch application	Push-button
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Switch function	+ NO push-button
Number of rocker	1
Actuator	Push-button
Fixing mode	By screws
Marking	Without marking
Colour tint	Copper
Surface finish	Glossy
Rated current	6 A - 250 V AC 50/60 Hz
Protection type	Fuse 16 A
Number of terminals	1 screw 2 screwless terminals
Shape of screw head	Hexagonal
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	13 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	48 mm
Embedding depth	38 mm
Product weight	0.186 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Product certifications	NF CE
IP degree of protection	IP20