

Product data sheet

Specifications



S quence5 - dolly switch - double 2-way - 10 AX - Chrome

S800224CV

⚠ Discontinued on: Jul 26, 2021

⚠ End-of-service on: Aug 19, 2021

⚠ Discontinued

Main

Range Of Product	Sequence5
Product Or Component Type	Switch
Device Presentation	Complete product
Switch Additional Information	With internal power connection
Switch Application	On/off switching
Type Of Packing	Box
Quantity Per Set	Set of 1
Sale Per Indivisible Quantity	1

Complementary

Device Mounting	Flush
Switch Function	2-way
Number Of Rocker	2
Actuator	Small dolly rocker
Fixing Mode	By screws
Colour Tint	Chrome
Surface Finish	Glossy
Rated Current	10 AX at 250 V AC 50 Hz
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un with cos ϕ = 0.3
Service Life In Cycles	20000 cycles at ON and OFF at rated voltage with cos ϕ = 0.6
Electrical Durability	20000 cycles at ON and OFF at rated voltage with cos ϕ = 0.6
Number Of Terminals	3 screwless terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for rigid cable(s) 1 x 1.5...2 x 2.5 mm ² for flexible cable(s) 1 x 1.5...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	12 mm
Material	Metal
Height	80 mm
Width	160 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	35 mm
Net Weight	0.47 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	5...35 °C
Standards	EN 60669-1 2006/95/EEC
Product Certifications	LCIE: CCA-FR_598285B LCIE: NF 604950 NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Alcohol Bleach UV resistant Acetone Petrol Window-cleaning fluid Oil Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	12 cm
Package 1 Length	18 cm
Package 1 Weight	525 g

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	