



Main

Range of product	Sequence5
Product or component type	Switch
Device presentation	Complete product
Switch application	Roller blind
Switch additional information	Mechanical and electrical interlock between up/down
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Switch function	3 positions
Number of rocker	3
Actuator	Push-button
Fixing mode	By screws
Colour tint	Brushed gold
Surface finish	Glossy
Rated current	6 AX - 250 V AC 50/60 Hz
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un
Number of terminals	3 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² stranded cable(s) 1 x 1.5...2 x 2.5 mm ² flexible cable(s) 1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	50.5 mm
Embedding depth	42 mm
Product weight	0.308 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	NF N LCIE : NF 604950 Aenor : 030/2257
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free