



Main

Range of product	Sequence5
Product or component type	Switch
Device presentation	Complete product
Switch additional information	With internal power connection
Switch application	On/off switching
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Switch function	2-way
Number of rocker	4
Actuator	Small dolly rocker
Fixing mode	By screws
Colour tint	Copper
Surface finish	Glossy
Rated current	10 AX - 250 V AC 50 Hz
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un with $\cos \varphi = 0.3$
Service life in cycles	20000 cycles @ ON and OFF at rated voltage with $\cos \varphi = 0.6$
Electrical durability	20000 cycles @ ON and OFF at rated voltage with $\cos \varphi = 0.6$
Number of terminals	3 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² stranded cable(s) 1 x 1.5...2 x 2.5 mm ² flexible cable(s) 1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	12 mm
Material	Metal
Height	80 mm
Width	320 mm
Depth	49 mm
Embedding depth	35 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product weight	0.705 kg
----------------	----------

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	NF LCIE : NF 604950 LCIE : CCA-FR_598285B
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free