



Main

Range of product	Sequence5
Product or component type	Push-button
Device presentation	Complete product
Switch additional information	Impulse relay control
Switch application	Push-button
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Switch function	Push-button
Number of rocker	4
Actuator	Small dolly rocker
Fixing mode	By screws
Marking	Without marking
Colour tint	Bronze
Surface finish	Glossy
Rated current	10 A - 250 V AC 50/60 Hz
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 U _n with cos φ = 0.3
Service life in cycles	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Electrical durability	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Number of terminals	2 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² stranded cable(s) 1 x 1.5...2 x 2.5 mm ² flexible cable(s) 1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	12 mm
Material	Metal
Height	320 mm
Width	80 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	35 mm
Product weight	0.94 kg

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	NF N LCIE : NF 604950 Aenor : 030/2237
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free