

Product data sheet

Specifications



Séquence5 - four push-button dolly - 10 A - Bronze

S800246BM

⚠ Discontinued on: Jul 26, 2021

⚠ End-of-service on: Aug 19, 2021

⚠ Discontinued

Main

Range Of Product	Sequence5
Product Or Component Type	Push-button
Device Presentation	Complete product
Switch Additional Information	Impulse relay control
Switch Application	Push-button
Type Of Packing	Box
Quantity Per Set	Set of 1
Sale Per Indivisible Quantity	1

Complementary

Device Mounting	Flush
Switch Function	Push-button
Number Of Rocker	4
Actuator	Small dolly rocker
Fixing Mode	By screws
Marking	Without marking
Colour Tint	Bronze
Surface Finish	Glossy
Rated Current	10 A at 250 V AC 50/60 Hz
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un with cos φ = 0.3
Service Life In Cycles	20000 cycles at ON and OFF at rated voltage with cos φ = 0.6
Electrical Durability	20000 cycles at ON and OFF at rated voltage with cos φ = 0.6
Number Of Terminals	2 screwless terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for rigid cable(s) 1 x 1.5...2 x 2.5 mm ² for flexible cable(s) 1 x 1.5...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	12 mm
Material	Metal
Height	320 mm
Width	80 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	49 mm
Embedding Depth	35 mm
Net Weight	0.94 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product Certifications	AENOR: 030/2237 LCIE: NF 604950 N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Window-cleaning fluid UV resistant Liquid soap Acetone Bleach Petrol Alcohol Oil

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	28 cm
Package 1 Length	35 cm
Package 1 Weight	1154 g

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)