



### Main

Range of product	Sequence5
Product or component type	Push-button
Device presentation	Complete product
Switch additional information	Impulse relay control
Switch application	Push-button
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

### Complementary

Device mounting	Flush
Switch function	Push-button
Number of rocker	4
Actuator	Small dolly rocker
Fixing mode	By screws
Marking	Without marking
Colour tint	Brushed gold
Surface finish	Glossy
Rated current	10 A - 250 V AC 50/60 Hz
Minimum load breaking capacity	200 operations 1.25 I <sub>n</sub> and 1.1 U <sub>n</sub> with cos φ = 0.3
Service life in cycles	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Electrical durability	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Number of terminals	2 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> stranded cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> flexible cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> rigid cable(s)
Wire stripping length	12 mm
Material	Metal
Height	320 mm
Width	80 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	35 mm
Product weight	0.94 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	NF N LCIE : NF 604950 Aenor : 030/2237
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Window-cleaning fluid Acetone Alcohol Bleach Oil UV resistant Liquid soap Ammonia Petrol
Environmental health and issues	Halogen free