



Main

| | |
|-------------------------------|------------------|
| Range of product | Sequence5 |
| Product or component type | 2 socket-outlets |
| Device presentation | Complete product |
| Type of packing | Box |
| Quantity per set | 1 |
| Sale per indivisible quantity | 1 |
| Number of terminals | 3 |

Complementary

| | |
|------------------------------|--|
| Device mounting | Flush |
| Outlet poles configuration | 2P + E with shutters |
| Outlet standard description | Pin earth |
| Outlet standard | French |
| Fixing mode | By screws |
| Colour tint | Bronze |
| Surface finish | Glossy |
| Rated current | 16 A - 250 V AC 50 Hz |
| Service life in cycles | 5000 cycles |
| Electrical durability | 5000 cycles |
| Connections - terminals | Screwless terminals |
| Shape of screw head | Pozidriv No 1 |
| Clamping connection capacity | 1 x 1.5...2 x 4 mm ² rigid cable(s) 1 x 1.5...2 x 4 mm ² stranded cable(s) 1 x 1.5...2 x 4 mm ² flexible cable(s) |
| Wire stripping length | 12 mm |
| Material | Metal |
| Height | 80 mm |
| Width | 160 mm |
| Depth | 39.5 mm |
| Embedding depth | 35 mm |
| Product weight | 0.334 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -5...50 °C |
| Dielectric strength | 2000 V |
| Ambient air temperature for operation | 5...35 °C |
| Standards | NF C 61-314 |
| Product certifications | NF LCIE : NF 603415A |
| IK degree of protection | IK04 |
| IP degree of protection | IP21D |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid |
| Environmental health and issues | Halogen free |