



### Main

|                               |                       |
|-------------------------------|-----------------------|
| Range of product              | Sequence5             |
| Product or component type     | Push-button           |
| Device presentation           | Complete product      |
| Switch additional information | Impulse relay control |
| Switch application            | Push-button           |
| Type of packing               | Box                   |
| Quantity per set              | Set of 1              |
| Sale per indivisible quantity | 1                     |

### Complementary

|                                |                                                                                                                                                                |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting                | Flush                                                                                                                                                          |
| Switch function                | Push-button                                                                                                                                                    |
| Number of rocker               | 4                                                                                                                                                              |
| Actuator                       | Small dolly rocker                                                                                                                                             |
| Fixing mode                    | By screws                                                                                                                                                      |
| Marking                        | Without marking                                                                                                                                                |
| Colour tint                    | Copper                                                                                                                                                         |
| Surface finish                 | Glossy                                                                                                                                                         |
| Rated current                  | 10 A - 250 V AC 50/60 Hz                                                                                                                                       |
| Minimum load breaking capacity | 200 operations 1.25 I <sub>n</sub> and 1.1 U <sub>n</sub> with cos φ = 0.3                                                                                     |
| Service life in cycles         | 20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6                                                                                                    |
| Electrical durability          | 20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6                                                                                                    |
| Number of terminals            | 2 screwless terminals                                                                                                                                          |
| Shape of screw head            | Pozidriv No 1                                                                                                                                                  |
| Clamping connection capacity   | 1 x 1.5...2 x 2.5 mm <sup>2</sup> stranded cable(s)<br>1 x 1.5...2 x 2.5 mm <sup>2</sup> flexible cable(s)<br>1 x 1.5...2 x 2.5 mm <sup>2</sup> rigid cable(s) |
| Wire stripping length          | 12 mm                                                                                                                                                          |
| Light source                   | LED 1.5 mA                                                                                                                                                     |
| Local signalling               | Lightable                                                                                                                                                      |
| Material                       | Metal                                                                                                                                                          |
| Height                         | 320 mm                                                                                                                                                         |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                 |          |
|-----------------|----------|
| Width           | 80 mm    |
| Depth           | 49 mm    |
| Embedding depth | 35 mm    |
| Product weight  | 0.952 kg |

## Environment

|                                       |                                                                                                                  |
|---------------------------------------|------------------------------------------------------------------------------------------------------------------|
| Ambient air temperature for storage   | -5...50 °C                                                                                                       |
| Dielectric strength                   | 2000 V                                                                                                           |
| Ambient air temperature for operation | 5...35 °C                                                                                                        |
| Standards                             | 2006/95/EEC<br>EN 60669-1                                                                                        |
| Product certifications                | NF<br>N<br>LCIE : NF 619318A<br>Aenor : 030/2237                                                                 |
| IK degree of protection               | IK04                                                                                                             |
| IP degree of protection               | IP21D                                                                                                            |
| Environmental characteristic          | Acetone<br>Alcohol<br>Ammonia<br>Bleach<br>Liquid soap<br>Oil<br>Petrol<br>UV resistant<br>Window-cleaning fluid |
| Environmental health and issues       | Halogen free                                                                                                     |